

# Table Top Rack Cabinets (RCHS Series) - *HEAVY DUTY*



Textured - Light Gray (RAL7035)

ſ

## <u>Features:</u>

- Heavy duty, 16-gauge steel, 19" table top rack cabinet...
- For ventilated versions link to our <u>RCHV</u> <u>series</u>...
- Panel rails are infinitely adjustable (front to back), round hole punched for 10-32 clip-nuts to full EIA hole centers (5/8 5/8 1/2 inch spacing)...
- Includes two pairs of rails (for rear support of heavier equipment), rubber feet, black ABS plastic handles, a starter pack of 10-32 clip nuts & matching **1421ABK** black screws...
- Supplied unassembled (four cabinet pieces & four rails), shipped in a flat pack container for handling ease & protection (see photo below)...
- Simple assembly using one bolt in each corner to lock the sides to the top and bottom (hardware included)...
- Overall width 21"...
- Overall height 2" over panel space...
- Front & back lip is .585" so usable depth is reduced by 1.17"
- Recommended maximum weight (RCHS1902824 tested) 800 pounds...
- Rugged textured powder paint finish...
- Stocked in Black & Light Gray (RAL7035)...

#### 17.5" Deep models:

٦٢

1

٦٢

٦

Part Number	Color	Deader File	duf Eilo	Panel I Inches		Number of Clip Nuts Included	
RCHS1900817BK1 RCHS1900817CG1 RCHS1900817LG1	Beige	63K	ZIP 59K	8.75	5	8	38
RCHS1901017BK1 RCHS1901017CG1 RCHS1901017LG1	Beige	60K	ZIP 61K	10.50	6	16	40
RCHS1901417BK1 RCHS1901417CG1 RCHS1901417LG1	Beige	64K	ZIP 60K	14.00	8	16	44
RCHS1901717BK1 RCHS1901717CG1 RCHS1901717LG1	Beige	67K	ZIP 63K	17.50	10	16	50
RCHS1902217BK1 RCHS1902217CG1 RCHS1902217LG1	Beige	70K	ZIP 65K	22.75	13	16	54
RCHS1902817BK1 RCHS1902817CG1 RCHS1902817LG1	Beige	72K	ZIP 67K	28.00	16	16	60

## 24.5" Deep models:


Part Number	Color	Sec.	dyf Filo	Panel H	leight	Number of Clip Nuts	
		Reader File	(zipped)	Inches	Units	I - I	
RCHS1901024BK1	Black	POF					
RCHS1901024CG1		Þ	ZIP	10.50	6	16	52
RCHS1901024LG1		68K	60K				
RCHS1901424BK1			710				
RCHS1901424CG1	Light Gray	100	ZIP	14.00	8	16	58
RCHS1901424LG1			60K				
RCHS1901724BK1		FDF	ZIP				
RCHS1901724CG1				17.50	10	16	62
RCHS1901724LG1		64K	60K				
RCHS1902224BK1			ZIP				
RCHS1902224CG1	Beige			22.75	13	16	70
RCHS1902224LG1	Light Gray	66K	60K				

RCHS1902824BK1 Black RCHS1902824CG1 Beige	FOF	ZIP	28.00	16	16	78
RCHS1902824CG1 Light Gra	<b>y</b> 82K	60K	20.00	10	10	70

### 31.5" Deep models:

Part Number	Part Number Color		dyf File		leight	Number of Clip Nuts	
		Reader File	(zipped)	Inches	Units	Included	
RCHS1901031BK1 RCHS1901031LG1		62K	ZIP 54K	10.50	6	16	64
RCHS1901431BK1 RCHS1901431LG1		63K	ZIP 54K	14.00	8	16	68
RCHS1901731BK1 RCHS1901731LG1		63K	ZIP 53K	17.50	10	16	74
RCHS1902231BK1 RCHS1902231LG1		65K	ZIP 53K	22.75	13	16	86
RCHS1902831BK1 RCHS1902831LG1		66K	ZIP 54K	28.00	16	16	94

## Feature Views:





## Accessories:



#### Casters - Part Number 1425PHD

#### • SOLD IN A SET OF 4

- Base of cabinet is punched to accept this caster set
- 600# Mfg's specified weight capacity (Set of 4)
- Features ball bearing swivel and hard composition wheels
- Small foot print 2.125" x 15/16" hole mounting pattern
- Wheels are grey & 2" wheel diameter (adds only 2.5" to overall rack height).
- Includes mounting hardware



#### Doors

- 16-gauge steel construction
- Both front & back of "RCHS" rack cabinets are punched to accept these doors
- Mounts either right or left hand hinge (door & cabinet are symmetrical)
- Includes installed lock and two keys
- Finished in rugged textured powder paint to match RCHS/RCHV enclosures
- Includes mounting hardware



		File	(zipped)	Panel Height	105.
RCHD1908DK1 RCHD1908CG1	Black Beige Light Gray	17K	ZIP 17K	8" (5 U)	5
RCHD1910BK1 RCHD1910CG1 RCHD1910LG1	Black Beige Light Gray	18K	ZIP 18K	10.5" (6 U)	5
RCHD1914BK1 RCHD1914CG1 RCHD1914LG1	Black Beige Light Gray	<b>19</b> K	ZIP 20K	14" (8 U)	6
	Black Beige Light Gray	21K	ZIP 22K	17.5" (10 U)	7
RCHD1922BK1 RCHD1922CG1 RCHD1922LG1	Black Beige Light Gray	22K	ZIP 24K	22.75" (13 U)	9
RCHD1928BK1 RCHD1928CG1 RCHD1928LG1	Black Beige Light Gray	24K	ZIP 27K	28" (16 U)	12



#### **Extra Panel Rails**

- RCHS rack cabinets ship with two pair order below for extra mounting capabilities
- Sold in pairs
- Finished in rugged black textured powder paint
- Includes amhal strut mounting hardware (black clip nuts are not included)

Part Number	Use With Cabinet Panel Height
<b>RCHR1908</b>	8" (5 U)
<b>RCHR1910</b>	10.5" (6 U)
<b>RCHR1914</b>	14" (8 U)
<b>RCHR1917</b>	17.5" (10 U)
<b>RCHR1922</b>	22.75" (13 U)



click to enlarge

#### **Extra Spring Nuts - Part Number 1421SN**

- 1/4 20 Strut nut
- 1/4 20 x 1/2 bolt
- Used only in our RCHS & RCHV table top rack cabinets handy for mounting of other equipment to the horizontal struts
- Sold in packages of 8 (8 spring nuts and 8 bolts) as shown



click to enlarge

# Replacement Rubber Feet - Part Number 1421RC24

- RCHS rack cabinets ship with four feet included - order these for replacement
- Sold in package of 20

