

## Knockdown Stacking Rack Cabinet *RCSC Series*



Ideal for AV or IT/Server applications, the RCSC Rack Cabinet features a stacking design that allows for up to three (3) cabinets\* to be stacked atop each other. This Rack Cabinet is fully loaded and includes two (2) pairs of infinitely adjustable sliding EIA square-hole rails, punch-outs for cable entry and/or fan cooling and comes in a variety of sizes and depths.

The unique stacking feature enables your cabinet space to grow as your needs do \*Stack up-to three (3) 12U, two (2) 24U or one (1) of each cabinet atop each other using the required **RCSCBAY** baying kit. The 12U cabinet is a great starter cabinet for any small to medium sized business.

### Features

- Constructed in 16-gauge steel.
- Includes two (2) pair of 19" EIA-310-D compliant square-hole mounting rails with rack unit markings.
- Four (4) embosses are included with support for optional levelling feet or casters.
- Grounding studs provided on body.
- The top and bottom of the RCSC includes two (2) laser knockouts (per side) for cable-entry or fans (includes gasket strip material).
- Includes a laser knockout rear gland plate for floor-level cable entry.
- Finished in rugged black powder paint.
- Ships unassembled in a flat pack container for easy handling and shipping protection.

### Specifications

- Mounting rails are infinitely adjustable in depth and are fabricated of heavy duty 14-gauge steel, painted smooth black.
- Optional doors are available in solid, tinted acrylic with venting (see above-left) and high airflow vented.
  - Snap-in hinges can be mounted without having to bolt-on from inside the cabinet. In addition, the hinges can be mounted on the left or right.
- High airflow perforated doors for both front and rear of the cabinet are suggested for most server applications.
  - Perforated doors meet server manufacturer Free-Air-Ratio (FAR) requirements at 63%.
- For 36" depth cabinet side panels include cable entry knockouts.
- Tested to nearly double the suggested load rating of 1,500 lbs.
- RoHS Compliant.
- Manufactured in North America.

### Gallery



## Accessories

**Universal Rack Shelf**

**Rack Mount Locking Storage  
Drawer**

**Sliding Keyboard Shelf**

**Rack Unit Label**

**Horizontal Lacing Strip**

**Horizontal Ring Cable Manager**

**Mounting Hardware**

**Caster Set**

**Grill Fan Kits**

**Adjustable Depth 4-Post Rack  
Mount Shelf**

**Four Post Mounting Sliding Shelf**

**Outlet Strips**

**Adjustable Depth Cable Manager**

**Horizontal Hinged Cable Manager**

**Horizontal Steel Finger Cable  
Manager**

**Rack Panels**

**Grounding**

**Leveling Feet**

| Part No.       | Overall Dimensions |       |       | Usable Mounting Dimensions |       |       | Rack<br>Units | Shipping<br>Weight |
|----------------|--------------------|-------|-------|----------------------------|-------|-------|---------------|--------------------|
|                | Height             | Width | Depth | Height                     | Width | Depth |               |                    |
| RCSC1902124BK1 | 25.00              | 24.00 | 24.50 | 21.00                      | 19.00 | 22.99 | 12U           | 86 lb (39.1 kg)    |
| RCSC1902131BK1 | 25.00              | 24.00 | 31.50 | 21.00                      | 19.00 | 29.99 | 12U           | 100 lb (45.5 kg)   |
| RCSC1902136BK1 | 25.00              | 24.00 | 36.00 | 21.00                      | 19.00 | 29.99 | 12U           | 110 lb (50.0 kg)   |
| RCSC1904224BK1 | 46.00              | 24.00 | 24.50 | 42.00                      | 19.00 | 22.99 | 24U           | 120 lb (54.5 kg)   |
| RCSC1904231BK1 | 46.00              | 24.00 | 31.50 | 42.00                      | 19.00 | 29.99 | 24U           | 145 lb (65.9 kg)   |
| RCSC1904236BK1 | 46.00              | 24.00 | 36.00 | 42.00                      | 19.00 | 29.99 | 24U           | 135 lb (61.4 kg)   |

## Optional Doors

| Part No.       | Part No.       | Part No.           | Use with Cabinet Panel Height |            |
|----------------|----------------|--------------------|-------------------------------|------------|
| Solid Door     | Vented Door    | Vented Window Door | Units                         | Rack Units |
| RCSC19021SDBK1 | RCSC19021VDBK1 | RCSC19021WDBK1     | 21.00                         | 12U        |
| RCSC19042SDBK1 | RCSC19042VDBK1 | RCSC19042WDBK1     | 42.00                         | 24U        |

## RCSC Baying Kit

|          |         |
|----------|---------|
| Part No. | RCSCBAY |
|----------|---------|

*Data subject to change without notice*