

Type 1 Lay In Screw Cover Wireway - w/o Knockouts cwsc NK

Series



A=12"	A=18"	A=24"	A=36"	A=48"
CWSC212NK	-	CWSC224NK	CWSC236NK	CWSC248NK
CWSC412NK	CWSC418NK	CWSC424NK	CWSC436NK	CWSC448NK
CWSC612NK	CWSC618NK	CWSC624NK	CWSC636NK	CWSC648NK
CWSC812NK	CWSC818NK	CWSC824NK	CWSC836NK	CWSC848NK
CWSC1012NK	-	CWSC1024NK	CWSC1036NK	CWSC1048NK
CWSC1212NK	-	CWSC1224NK	CWSC1236NK	CWSC1248NK



A=60"	A=72"	A=96"	A=120"	В
CWSC260NK	-	-	CWSC2120NK	2.50
CWSC460NK	CWSC472NK	-	CWSC4120NK	4.00
CWSC660NK	CWSC672NK	-	CWSC6120NK	6.00
CWSC860NK	CWSC872NK	-	CWSC8120NK	8.00
CWSC1060NK	CWSC1072NK	CWSC1096NK	CWSC10120NK	10.00
CWSC1260NK	CWSC1272NK	CWSC1296NK	CWSC12120NK	12.00

Data subject to change without notice