

Available while supplies last

HAMMOND MANUFACTURING.

Note: This product line has been discontinued as a stocked series. Information is for reference only. It has been replaced with **RB-DC Series**. For alternative solution assistance, please contact Hammond Customer Service - **sales@hammfg.com** or USA (716) 630-7030, Canada and International (519) 822-2960.



RACK BASICS[®]







The DC200 series cabinets are offered in two capacities, 24U spaces and 42U spaces. A standard overall width of 23.6" (24") allow cabinets to side or bay together matching standard 2ft floor tile placement, optimizing sub-floor cable and cold-air access without conflict.

Looking for a deal? There are DC200 products in our Clearance Section. Click here to learn more.

Features

- Constructed in 16-gauge steel.
- Two pairs of 19" EIA-310-D compliant square hole punched rails with rack unit markings.
 - Starter pack of M5 screws and cage nuts included.
 - For 10-32 hardware see the **1421CNABK Series**.
- Locking front door has attractive 4 point latch, curved and ribbed surface for added stability, and can be easily removed and hinged in either direction.
- Rear of cabinet features split locking doors making access easier in tight spaces.
- Pair of removable solid side panels include stiffeners for added strength.

Specifications

- Includes two (2) 4" diameter cable entry holes (top) and one (1) 8" x 12" opening (bottom).
- Open frame bottom allows raised tile floor cable and air access.
- Bottom of cabinet includes:
 - Four (4) adjustable leveling feet
 - Four (4) recessed casters
- Rails can adjust in depth in 25mm increments.
- Grounding studs provided on frame.
- Finished in smooth black powder paint.
- Tested to nearly double the suggested load rating of 950 lbs..
- RoHS Compliant.

Part of the Rack Basics® line of economy rack solutions.

Gallery



Accessories

- Universal Rack Shelf
- Rack Mount Locking Storage Drawer
- Sliding Keyboard Shelf
- Rack Unit Label
- Horizontal Lacing Strip
- Horizontal Hinged Cable Manager
- Cable Management Arm
- Rack Panels

- Adjustable Depth 4-Post Rack Mount Shelf
- Four Post Mounting Sliding Shelf
- Outlet Strips
- Adjustable Depth Cable Manager
- Horizontal Ring Cable ManagerHorizontal Steel Finger Cable
- Manager
- Outlet Strips
- Mounting Hardware

	Overall Dimensions			Rack	Usable Mounting Dimensions			Shipping
Part No.	Height	Width	Depth	Units	Height	Width	Depth	Weight
DC2004224	47.10	23.60	43.40	24U	42.00	19.00	38.00	280 lb
DC2004242	78.60	23.60	43.30	42U	73.50	19.00	38.00	385 lb

DC200 Specific Accessories

Part No.	Description			
DC2PBCLP	Accessory mounting bracket for Hammond vertical outlet strips and cable managers			
DC200PR24	Pair of 24U Square Hole Mounting Rails			
DC200PR42	Pair of 42U Square Hole Mounting Rails			

Compatible Vertical Cable Managers

Part No.	Description		
C4VCM73BK1	Vertical Cable Manager with Hinged Door		
VCT73	Vertical Cable Tray		
VCTPDU73	Vertical Cable Tray with Tooless PDU Cutouts.		

Data subject to change without notice

© 2015. Hammond Manufacturing Ltd. All rights reserved.