

Heavy Duty Steel Knockdown 4-Post Open Frame

Rack DC4R Series

Adjustable Depth











The all new Hammond DC4R Open Rack series is one of the most economical solutions to house IT equipment in wiring closets or data centers. In situations where the wiring closet itself is under lock and key and accessed by a limited number of people, full cabinets having locking doors and side panels may not be required resulting in a significant cost savings.

Standard Features

- Available in 24U and 44U and in two convenient adjusting depths.
 - 24"-36" for standard rackmount equipment.
 - 32"-48" for extra deep equipment.
- Includes two (2) pairs of 19" mounting EIA-310-D compliant square-hole rails.
 - Optional pair of rails available for multiple mounting depths.
- Mounting rails include permanent rack unit space indicators.
- Rail depth L-bracket restrict the installer from over-extending the rack. This ensures the integrity of the rack.
- Self-squaring design for a short assembly time.
- Includes one (1) set of two (2) horizontal cable manager bars. Additional cable manager bars available by ordering part number DC4RSHCM.
- Finished in smooth black powder paint.
- Knockdown design ships un-assembled for easy handling and shipping protection.

Specifications

- Constructed of 12-gauge steel.
- Suggested load capacity of 2,000 lb.
- RoHS Compliant.
- Manufactured in North America.

Updates

- **05-May-2014:** The DC4R series now includes four (4) pairs of integrated 10-32 ground studs, at both the front and rear of the rack. Stud pairs are conveniently spaced 5/8" apart and located across from each other inside the rail channel. For added convenience, two (2) pairs are located near the top of the rack, while the others are near the bottom of the rack. This upgrade ensures a secure and easy ground lug attachment.
- 23-Apr-2014: As an added value, the DC4R Series will soon ship with a 50 pack of screws and cage nuts (1421CNABK50). This is a rolling change and while appear as stock becomes available.

Accessories

<u>Universal Rack Shelf</u> <u>Two Post Mounting Adjustable Shelf</u>

Two Post Mounting Keyboard & Monitor Rack Mount Locking Storage Drawer

Shelf

Sliding Keyboard Shelf Four Post Mounting Adjustable Depth

Shelf

Four Post Mounting Sliding Shelf Outlet Strips

<u>Hinged Acrylic Door Panel Cover</u> <u>Adjustable Depth Cable Manager</u>

<u>Vertical Fingered Rack Cable Manager</u> <u>Cable Management</u>

with Door

Mounting Hardware Rack Panels

<u>Grounding</u> <u>Light Duty Caster Set for Open Frame</u>

<u>Rack</u>

Rack Unit Label Rack and Cabinet

Baying/Ganging/Joining Kit

Bolt Down Kit

	Overall Dimensions		Rack	Mounting Dimensions			
Part No.	Height	Width	Units	Height	Width	Min Depth	Max Depth
DC4R24	48.12	20.50	24U	42.00	19.00	24.00	36.00
DC4R2448	48.12	20.50	24U	42.00	19.00	32.00	48.00
DC4R44	83.13	20.50	44U	77.00	19.00	24.00	36.00
DC4R4448	83.13	20.50	44U	77.00	19.00	32.00	48.00

The base feet extending outwards add approx. 12 inches of overall depth.

DC4R Specific Accessories

Part No.	Description
DC4RSHCM	Additional Horizontal Cable Bars (2)
DC4RPR24	Additional pair of rails for DC4R 24U
DC4RPR44	Additional pair of rails for DC4R 44U

Data subject to change without notice

© 2014. Hammond Manufacturing Ltd. All rights reserved.