

- ► Replaces cumbersome Post and Stack lights.
- ▶ Position conveniently near the operator.
- ▶ Straight and right-angle enclosures.
- ▶ Programmable for multiple colors and flashing functions in a single light (most models).
- ► Each light contains three colors; red, yellow, green - optional colors available.

- machine mounting.
- ► Rugged, solid-state design eliminates bulb replacement.
- ► Euro-style, 4-pin QD connection; no soldering or moisture issues.
- ► Compatible with PLC or other logic-level control outputs.
- ▶ Install without certified personnel.
- ▶ Non-programmable models available.

Three Housing Styles Three colors in each light.







bannerengineering.com


Applications for EZ-LIGHT™



STOP Mode



BAD Part



Process Identification



Pick-to-Light

Replace Soldered Panel Indicators & Oil-Tight Lights



1.866.816.5187



more sensors, more solutions

EZ-LIGHT™ Indicators


EZ-LIGHT Models

Model

M18SL1Q

T30SL1Q

T18DL1Q



^{*}Integral cable models also available. Contact factory or go online for more information.

Housing Style/Mounting

In-Line, 18 mm barrel

Right-Angle, 30 mm barrel

Right-Angle, 18 mm barrel




Programmable for Seven Light and Flash Functions*

Red, Green, Yellow Light

Models M18 T30 T18			Light/Flash	Hookup†	Function
•	•	•	(1 0 +	Red glows steady
•	•			1 0 +	Red flashes
•	•	•	6	<u>2</u>	Yellow glows steady
•	•		8	2	Yellow flashes
•	•	•	\	<u>4</u> • • • •	Green glows steady
•	•			2	Green flashes
•	•			4 0 0 +	Red, Green, Yellow flash cycle


^{*}Model T18DL1Q not programmable

EZ-LIGHT Hookup[†]



[†] Wiring key: 1 = Brown; 2 = White; 3 = Blue; 4 = Black

EZ-LIGHT Quick Disconnect (QD) Cables



EZ-LIGHT Mounting Brackets

Model	Use With	Description
SMB18A	M18, T18	12-gauge stainless steel, right angled bracket with a curved mounting slot for versatility and orientation
SMB30A	T30	



