

Search Banner

[Home](#)[About Banner](#)[Products & Applications](#)[Product Support](#)[News & Events](#)[Cart](#)[B](#)

Product Support

Part & Model Reference

[Model & Part Search](#)[Videos](#)[Technical Literature](#)[Software](#)[CAD Files](#)[Catalogs](#)[Brochures](#)[Product Warranty](#)[Tools & Tutorials](#)[Worldwide Locations](#)[SISTEMA Library](#)

MQDC-515 P/N 30623

Micro-style Quick Disconnect Cable
5-Pin Straight Connector
5 m (15 ft) in Length

[Specifications](#)[Family Overview](#)

Specifications

Primary Connector Type	MICRO
Coupling Method	1/2"-20 Dual Key
Number of Pins	5
Gender	Female
Orientation	Straight
Length (m)	5
Connector Body Material/Color	PUR Black

Number of Connectors	1
Number of Wires	5
Secondary Connector Type (or Branch 1 connector)	Flying Leads
Gauge (AWG)	22
Cable Jacket Material	PVC
Cable Jacket Color	Black
Outside Cable Diameter (mm)	5.6
Shield	No Shield
AC Voltage/current	250V/4A
DC Voltage/current	250V/4A
Minimum Temp. (Celsius)	-40
Maximum Temp. (Celsius)	105
IEC IP67	Y
IEC IP68	N
IEC IP69K	N

Banner Insider eNewsletter

Helpful application information, new product updates, answers to frequently asked questions, and more.

[Subscribe Now »](#)

Banner Enhances Mobile Site

m.bannerengineering.com »

Search by part/model number

Easily locate distributors in your area

Share data from your phone or tablet