

## Thermal transfer printer - THERMOMARK ROLLMASTER 300 - 0804501

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Thermal transfer printer, 300 dpi, incl. European power cable, US power cable, and USB cable. DVD with CLIP PROJECT advanced planning and marking software, user manuals in various languages, Windows® printer driver, and firmware. German/English user manual in DIN A5 format, EML (20x8)R roll of labels, white, with 1000 labels, and ink ribbon: 50 m

### Why buy this product

- ✓ The THERMOMARK ROLLMASTER 300 is an industrial printer for printing large quantities of marking materials in roll format. Print resolution of 300 dpi.
- ✓ Printing of punched and continuous adhesive labels, insert labels, and shrink sleeves
- ✓ Fast, high-quality, and durable printing
- ✓ Easy and intuitive operation via touch color display
- ✓ Easy and intuitive operation via touch color display
- ✓ Easy and flexible control by means of the multilingual CLIP PROJECT planning and marking software. With the option of direct entry or import of printing information from various data sources
- ✓ USB and Ethernet connections

RoHS

### Key Commercial Data

Packing unit	1 STK
GTIN	 4 055626 381619
GTIN	4055626381619
Custom tariff number	84433210
Country of origin	Germany

### Technical data

#### General

Interface	10/100 Mbps Ethernet
	USB 2.0
Weight	10 kg

## Thermal transfer printer - THERMOMARK ROLLMASTER 300 - 0804501

### Technical data

#### Dimensions

Length	460 mm
Height	288 mm
Width	380 mm

#### Connection data

Minimum voltage	100 V AC
Max. voltage	240 V AC

#### Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
China RoHS	Environmentally Friendly Use Period = 10;
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"