

## Test plugs - MPS-MT - 0201744

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Test plugs, with solder connection up to 1 mm<sup>2</sup> conductor cross section, color: silver

### Why buy this product

- The test plug reliably makes contact in the bridge shaft and in all test sockets with a 2.3 mm diameter
- Two-piece test plug for individual plug color combinations
- The test plugs are inserted in the function shaft of terminal blocks from the CLIPLINE complete system or in the test connections provided

RoHS

### Key Commercial Data

Packing unit	10 STK
Minimum order quantity	10 STK
GTIN	 4 017918 098803
GTIN	4017918098803

### Technical data

#### Dimensions

Length	5 mm
Length contact range	10.85 mm
Width	5 mm
Pitch	5 mm
Pin diameter	2.3 mm
Note on dimensions	Length without insulating sleeve

#### General

Color	silver
Material	silver-plated brass
Ambient temperature (operation)	-40 °C ... 125 °C
Nominal voltage U <sub>N</sub>	60 V DC (30 V AC)

# Test plugs - MPS-MT - 0201744

## Technical data

Nominal current $I_N$	10 A
-----------------------	------

## Environmental Product Compliance

China RoHS	Environmentally Friendly Use Period = 50
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

## Approvals

### Approvals

---

Approvals

EAC

---

Ex Approvals

---

### Approval details

EAC		EAC-Zulassung
-----	---	---------------

---

Phoenix Contact 2018 © - all rights reserved  
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG  
Flachsmarktstr. 8  
32825 Blomberg  
Germany  
Tel. +49 5235 300  
Fax +49 5235 3 41200  
<http://www.phoenixcontact.com>