

Insert strip - ESL 40X17 - 0808095

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Insert strip, Sheet, white, unlabeled, can be labeled with: Office printing systems, Plotter, Perforated, Mounting type: Insert, Lettering field: 40 x 17 mm

The illustration shows the insert strip with terminal strip marker carrier

Product Features

- Insert labels for plastic cable markers
- The material file can be downloaded under the CLIP PROJECT software under Downloads - "Software update - Marking".

Key commercial data

Packing unit	1 pc
Minimum order quantity	10 pc
Weight per Piece (excluding packing)	15.8 GRM
Custom tariff number	39206219
Country of origin	Germany

Technical data

Dimensions

Length (b)	40 mm
Width (a)	17 mm

Ambient conditions

Ambient temperature (operation)	-40 °C ... 100 °C
---------------------------------	-------------------

General

Note	Print image may vary depending on laser printer
Color	white
Components	free from silicone and halogen
Material	Polyester foil
Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Number of individual labels	56
Number of individual labels per row	4

Insert strip - ESL 40X17 - 0808095

Technical data

General

Marking mounting type	Insert
-----------------------	--------

Classifications

eCl@ss

eCl@ss 4.0	24190219
eCl@ss 4.1	24190219
eCl@ss 5.0	27141137
eCl@ss 5.1	27141137
eCl@ss 6.0	27141137
eCl@ss 7.0	27141137
eCl@ss 8.0	27141137

ETIM

ETIM 2.0	EC000761
ETIM 3.0	EC000761
ETIM 4.0	EC000761
ETIM 5.0	EC000761

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410