

SACC-M12MS-8CON-PG9-M

Order No.: 1513334

<http://eshop.phoenixcontact.de/phoenix/treeViewClick.do?UID=1513334>Sensor/actuator connector, male, straight, 8-pos., M12, A-coded,
screw connection, metal knurl, cable screw connection Pg9

Commercial data

EAN	4017918910938
Pack	1 pcs.
Customs tariff	85366990
Weight/Piece	0.0227 KG
Catalog page information	Page 45 (PC-2009)

Product notes

WEEE/RoHS-compliant since:
03/21/2006

<http://www.download.phoenixcontact.com>
Please note that the data given here has been taken from the online catalog. For comprehensive information and data, please refer to the user documentation. The General Terms and Conditions of Use apply to Internet downloads.

Technical data

General data

Nominal current I_N	2 A
Nominal voltage U_N	30 V
Number of positions	8
Volume resistance	$\leq 3 \text{ m}\Omega$
Insulation resistance	$\geq 100 \text{ M}\Omega$


Ambient temperature (operation)	-40 °C ... 85 °C (plug/socket)
Pg screw connection	Pg9

General characteristics

Coding	A - standard
Inflammability class acc. to UL 94	V0
Surge voltage category	II
Pollution degree	3
Degree of protection	IP67
Contact material	CuZn
Contact surface material	Au
Contact carrier material	PA 66
Material of grip body	PBT
Material, knurls	Zinc die-cast, (nickel-plated)
Sealing material	NBR
Type of connection	Screw connection
Conductor cross section stranded min.	0.25 mm ²
Conductor cross section stranded max.	0.75 mm ²
Conductor cross section AWG/kcmil min.	24
Conductor cross section AWG/kcmil max	18
Min. diameter	6 mm
Max. diameter	8 mm
Status display	No

Drawings


Dimensioned drawing



M12 x 1 male connector, straight

Schematic diagram

Pin assignment M12 plug, 8-pos., A-coded, view plug side



Address

PHOENIX CONTACT GmbH & Co. KG
Flachmarktstr. 8
32825 Blomberg, Germany
Phone +49 5235 3 00
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>



© 2009 Phoenix Contact
Technical modifications reserved;