

## Sealing cap - PROT-M12 FS - 1560251

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)




M12 sealing cap for unoccupied M12 plugs of the sensor/actuator cable, flush-type plugs and I/O devices in the field

### Product Features

- Sealing caps with external or inner thread
- Printed or unprinted marking labels



### Key commercial data

Packing unit	5 PCE
Minimum order quantity	5 PCE
GTIN	 4 046356 183659
Weight per Piece (excluding packing)	1.46 GRM
Custom tariff number	39235090
Country of origin	Germany

### Technical data

#### Ambient conditions

Degree of protection	IP67
----------------------	------

#### Material

Inflammability class according to UL 94	HB
Material of grip body	PA 6
Sealing material	NBR

### Classifications

#### eCl@ss

eCl@ss 4.0	272607xx
eCl@ss 4.1	27260701
eCl@ss 5.0	27149110

## Sealing cap - PROT-M12 FS - 1560251

### Classifications

#### eCl@ss

eCl@ss 5.1	27149110
eCl@ss 6.0	27061801
eCl@ss 7.0	27061801
eCl@ss 8.0	27061801

#### ETIM

ETIM 3.0	EC002040
ETIM 4.0	EC002040
ETIM 5.0	EC000830

#### UNSPSC

UNSPSC 6.01	30212113
UNSPSC 7.0901	39121712
UNSPSC 11	39121712
UNSPSC 12.01	39121712
UNSPSC 13.2	39121712

### Drawings

Dimensioned drawing

