

814-1895

HW1F-2F11QD-R-24V

22mm Selector Switch Lighted



Key Features

- Finger safe (IP20) screw terminals standard, other terminal styles available
- All E-Stops meet EN418 (IEC compliant, positive action)
- UL listed, CSA certified, TUV approved, and CE marked
- Super bright incandescent or LED illumination
- IP65 and NEMA type 1, 2, 3, 3R, 4, 4X, 5, 12, and 13
- 600V/10A contacts with a wide operating range from 5mA at 3V AC/DC to 10A at 120V AC



Operation Type	Maintained
Product Type	Selector Switch Illuminated
Mounting Hole Size	Φ22mm
Shape	Round
Color	Red
Normally Open Contacts	1
Normally Closed Contacts	1
Number of Positions	2

Illumination Voltage 24V AC|24V DC