



Home: Products: Wire Strippers: Adjustable Precision Wire Strippers



VIEW LARGER IMAGE >>

## **Adjustable Precision Wire Strippers**

These Precision Wire Strippers feature an adjustment dial that allows the operator to select one of six different settings.

A calibrated wire stop can then be adjusted for the desired insulation strip length. In a single motion, the operator squeezes and pulls the tool. This action engages four specially hardened blades to cleanly cut the wire insulation while the pulling motion breaks the insulation / conductor bond.

- Adjustable to six wire gauges: ST-450 26 to 36 AWG ST-500 20 to 30 AWG ST-500ESD 20 to 30 AWG ST-550 18 to 28 AWG
- Calibrated Wire Stop adjustable to 2" (50.8mm)
- Clean, precise strip of any insulation type
- Lightweight-weighs 1 oz.
- Blade is hardened steel (RC58)
- Dimensions 3.9" x 1.6" x 0.6"
  (99 mm x 42 mm x 14 mm)

INCHES METRIC				
Part No.	ST-450	ST-500	ST-500ESD	ST-550
Wire Gauge	26-36 AWG	20-30 AWG	20-30 AWG	18-28 AWG
Calibrated Wire Strip Length	Adjustable to 2"	Adjustable to 2"	Adjustable to 2"	Adjustable to 2"
Insulation Type	Any	Any	Any	Any
Dimensions (L x H x Thickness)	3.9' x 1.6" x 0.6'	3.9" x 1.6" x 0.6"	3.9" x 1.6' x 0.6'	3.9" x 1.6" x 0.6"
Housing Material	ABS	ABS	ESD Safe Polycarbonate	ABS
Blade	Hardened Steel (RC 58)	Hardened Steel (RC 58)	Hardened Steel (RC 58)	Hardened Steel (RC 58)