



[VIEW LARGER IMAGE >>](#)

-  [R24 Wire Specification](#)
-  [R26 Wire Specification](#)
-  [R28 Wire Specification](#)
-  [R30 Wire Specification](#)

Kynar® insulated silver plated copper wire

Ideally suited for wire wrapping and many other applications.

Ideally suited for many applications including production line work and wire wrapping. This wire is OFHC (oxygen free high conductivity) and provides a flexible yet abrasion resistant wire. The 24-28 AWG wire is UL 1422 (.005" insulation) and the 30 AWG wire is UL 1423 (.004" insulation). The wire is solid copper with 105° C maximum insulation temperature and all gauges are no voltage rated.

INCHES

METRIC

Wire Size AWG	Insulation Diameter Inches	Roll Size Feet	BLUE	YELLOW	WHITE	BLACK	RED
24	.030	100	R24B-0100	R24Y-0100	R24W-0100	R24BLK-0100	R24R-0100
26	.027	100	R26B-0100	R26Y-0100	R26W-0100	R26BLK-0100	R26R-0100
28	.024	100	R28B-0100	R28Y-0100	R28W-0100	R28BLK-0100	R28R-0100
30	.0195	100	R30B-0100	R30Y-0100	R30W-0100	R30BLK-0100	R30R-0100
		1000	R30B-1000	R30Y-1000	R30W-1000	R30BLK-1000	R30R-1000