

Products & Services

PRODUCTS

- Product Catalog
- Solderforms / Preforms
- Thermal Interface Materials
- Request For Quote
- Order Information

SERVICES

- Kester University
- Metal Analysis
- Solder Reclaim

Product Catalog

[Search Again](#)

[Product Information](#) | [Product Specifications](#) | [IPC](#) | [Part Numbers](#)

Product Information [Back to Top](#)

44

44 is a high activity RA core flux designed for excellent instant wetting action. Although "44" is a RA-based material, the residues are non-corrosive if not cleaned. Per J-STD-004 is classified as ROM1 flux.

[View Data Sheet \(English\)](#)

[Find MSDS](#)

[Request a Sample](#)

[Request a Quote](#)



Looking for a more flexible no-clean paste?

Kester's PureMark 202

Product Specifications [Back to Top](#)

Tensile Strength	see chart
Specific Gravity:	1.08

IPC [Back to Top](#)

Classification:	ROM1
SIR:	Pass
Halide Content:	0.44%
Copper Plate Corrosion:	M
Copper Mirror:	M

Part Numbers [Back to Top](#)

Alloy	Packaging	Americas	Asia Pacific	Europe	Japan	Brazil
Sn63Pb37	1 lb., 0.015" diameter, 66 core	24-6337-0007 UPC:	Contact Us	Contact Us	Contact Us	Contact Us
Sn63Pb37	1 lb., 0.020" diameter, 66 core	24-6337-0010 UPC:	Contact Us	Contact Us	Contact Us	Contact Us
Sn63Pb37	1 lb., 0.025" diameter, 66 core	24-6337-0018 UPC:	Contact Us	Contact Us	Contact Us	Contact Us
Sn63Pb37	1 lb., 0.031" diameter, 66 core	24-6337-0027 UPC:	Contact Us	Contact Us	Contact Us	Contact Us

Sn63Pb37	1 lb., 0.040" diameter, 66 core	24-6337-0039 UPC:	Contact Us	Contact Us	Contact Us	Contact Us
Sn63pb37	1 lb., 0.050" diameter, 66 core	24-6337-0053 UPC:	Contact Us	Contact Us	Contact Us	Contact Us
Sn63Pb37	1 lb., 0.062" diameter, 66 core	24-6337-0061 UPC:	Contact Us	Contact Us	Contact Us	Contact Us
Sn60Pb40	1 lb., 0.020" diameter, 66 core	24-6040-0010 UPC:	Contact Us	Contact Us	Contact Us	Contact Us
Sn60Pb40	1 lb., 0.025" diameter, 66 core	24-6040-0018 UPC:	Contact Us	Contact Us	Contact Us	Contact Us
Sn60Pb40	1 lb., 0.031" diameter, 66 core	24-6040-0027 UPC:	Contact Us	Contact Us	Contact Us	Contact Us
Sn60Pb40	1 lb., 0.040" diameter, 66 core	24-6040-0039 UPC:	Contact Us	Contact Us	Contact Us	Contact Us
Sn60Pb40	1 lb., 0.050" diameter, 66 core	24-6040-0053 UPC:	Contact Us	Contact Us	Contact Us	Contact Us
Sn60Pb40	1 lb., 0.062" diameter, 66 core	24-6040-0061 UPC:	Contact Us	Contact Us	Contact Us	Contact Us
Sn60Pb40	1 lb., 0.093" diameter, 66 core	24-6040-0066 UPC:	Contact Us	Contact Us	Contact Us	Contact Us
Sn63Pb37	¼ or ½ Kg Spool, 0.25-3.00mm, Core 50, 58 or 66	Contact Us	44 UPC:	Contact Us	Contact Us	Contact Us
Sn60Pb40	¼ or ½ Kg Spool, 0.25-3.00mm, Core 50, 58 or 66	Contact Us	44 UPC:	Contact Us	Contact Us	Contact Us
Ag2Sn62Pb36	¼ or ½ Kg Spool, 0.25-3.00mm, Core 50, 58 or 66	Contact Us	44 UPC:	Contact Us	Contact Us	Contact Us

