












Ordering Information

Optional accessories		
Measuring accessories (temperature)		
<p>U1180A Thermocouple adapter+lead kit, J and K types</p>		<p>Includes thermocouple adapter, thermocouple bead J-type and thermocouple bead K-type.</p> <ul style="list-style-type: none"> - T/C adapter J/K-type - T/C bead J-type: -20 °C to 200 °C - T/C bead K-type: -20 °C to 200 °C
<p>U1181A Immersion temperature probe</p>		<ul style="list-style-type: none"> - Type-K T/C for use in oil and other liquids - Measurement range: -50 °C to 700 °C - Includes adapter U1184A for connection to DMM
<p>U1182A Industrial surface temperature probe</p>		<ul style="list-style-type: none"> - Type-K T/C for use on still surfaces - Measurement range: -50 °C to 400 °C - Includes adapter U1184A for connection to DMM
<p>U1183A Air temperature probe</p>		<ul style="list-style-type: none"> - Type-K T/C for use in air and non-caustic gas - Measurement range: -50 °C to 800 °C - Includes adapter U1184A for connection to DMM
<p>U1184A Temperature probe adapter</p>		<ul style="list-style-type: none"> - Mini-connector-to-banana-plug adapter for use with DMM
<p>U1185A J-type thermocouple and adapter</p>		<ul style="list-style-type: none"> - T/C adapter J/K-type - T/C bead J-type: -20 °C to 200 °C
<p>U1186A K-type thermocouple and adapter</p>		<ul style="list-style-type: none"> - T/C adapter J/K-type - T/C bead J-type: -20 °C to 200 °C
Carrying case		
<p>U1172A Transit case (aluminium-clad)</p>		<p>The robust casing to transport your DMM and accessories</p> <ul style="list-style-type: none"> - Aluminum-clad, black panel construction - Dimension: 18 inches (H) x 13 inches (W) x 6 inches (D) - Weight: 4 kg
<p>U1174A Soft carrying case</p>		<p>The convenient way to carry your DMM and essential accessories</p> <ul style="list-style-type: none"> - Dimension: 9 inches (H) x 5 inches (W) x 3 inches (D)
Hanging kit		
<p>U1171A Magnetic hanging kit</p>		<p>For fastening the DMM to a steel surface so both hands are free</p>
<p>U1179A IR Connectivity Bracke</p>		<p>Connect with U1177A IR-to-Bluetooth adapter or U1173A IR-USB cable</p>