
## "Auto" Step Down - Plug In (175 Series)





## PLUG IN - STEP DOWN AUTOTRANSFORMERS (230V to 115V)

- Single winding, does not provide isolation, for use where equipment is already isolated and only voltage change is required.
- World wide applications, 50 or 60 Hz. operation, step down (230VAC to 115VAC).
- Input is circuit breaker protected.
- Hi-pot tested to 2 KV RMS.
- Standard 3-wire, grounded plug (can also be used with adaptors for proper grounding).
- Input connected to a 5 foot cord & grounded North American 250V 3-wire plug (NEMA 6-15P).
- Output connected to standard North American 115V - 3 wire grounded receptacle (NEMA 5-15R).
- North American Mark of Safety C UL & UL listed File #E211544
- Remember These units do NOT convert line frequency.

Part No.	Capacity	Dimensions (Inches)					Wt.
	VA	Α	В	С	D	E	Lbs.
175A-NA	100	3.16	4.25	3.81	2.50	2.94	3.5
175B-NA	200	3.16	4.50	3.81	2.50	3.19	4.5
175C-NA	300	3.16	5.00	3.81	2.50	3.69	6
175D-NA	500	3.80	6.00	4.68	3.00	4.38	10
175E-NA	750	3.80	7.06	4.68	3.00	5.38	14
175F-NA	1000	3.80	7.06	4.68	3.00	5.38	14.5
175G-NA	1500	4.40	6.63	5.39	3.50	6.09	22





CANADA Guelph, Ontario (519) 822-2960 St. Laurent, Quebec (514) 343-9010 USA Cheektowaga, NY (716) 630-7030

## www.hammondmfg.com

EUROPE Basingstoke, UK 01256 812812

AUSTRALIA Queenstown, Australia 61-8-8240-2244