




DATE	DESCRIPTION	REV.
8.10.00	CHANGE AS PER ECN 00-084	J
10.17.11	CHANGE AS PER ECN 11-134	K
2.09.16	CHANGE AS PER ECN 16-027	L



- NOTE:
1. HEAT TREAT TO SPRING TEMPER.
  2. DESIGNED TO CLIP OVER PANELS FROM .060 [1.52] THRU .070 [1.78] THK.
  3. \* DENOTES ±.015 [±.38] TOLERANCE



ACTUAL SIZE

<b>KEYSTONE ELECTRONICS CORP.</b>			
www.keystec.com • ASTORIA, N.Y. 11105-2017 • Tel (718) 956-8900			
PART NAME		DUAL 'A'-AA CONTACT	
MATERIAL			
.012 [.30] THK ANNEALED SPRING STEEL			
FINISH		NICKEL PLATE	
TOLERANCES		INCH [MM]	CODE
DECIMAL	± .010	[± 0.25]	C
ANGULAR	± 1°		
UNLESS OTHERWISE SPECIFIED			
DRN BY	BOONE	DATE	12.9.82
APP'D	LN	SCALE	3X
DWG NO.		<b>210</b>	