Varior - Potentiometer



EN 60529 Degree of Protection IP20

Variable Control Potentiometer LONG TREADLE THROW LARGE FOOTPRINT DESIGN

Materials of Construction:

- Steel housing electro-coated black finish
- Complete with full treadle pad and nonskid base pad
- Spring return pedal action on momentary models
- Adjustable friction pad design on maintained models
- Maximum resistance must be specified when ordering

Features & Benefits:

- Retrofits most welding equipment with a simple receptacle selection
- For environments where a non-watertight housing is suitable
- 2 holes provided for rigid mounting to floor or equipment
- Heel rest offered on "OH" models

Options:

- Custom cable lengths available
- Varior foot operated potentiometers are available with 5,000 Ohm or 10,000 Ohm values. Other potentiometer values are available upon request or by special order. Please contact the office for availability and pricing.



ESAB • HOBART • LINCOLN • MILLER WELDING EQUIPMENT REPLACEMENT FOOT CONTROLS

Standard				
Size (HxWxD):	4.17 x 4.50 x 9.71 In.			
Weight:	4.91 lbs.			
Industrial				
Size (HxWxD):	4.00 x 4.52 x 12.78 In.			
Weight:	5.00 lbs.			
	·			

For Dimension Drawings visit <u>www.linemaster.com</u> and click on Line Drawings located under the Guides & Literature Tab

NOTE:

Contact LINEMASTER® for replacement foot controls for your ESAB°, Hobart°, Lincoln° or Miller° welding equipment.

▲WARNING SEE PRODUCT WARNING ON PAGE 103						
SPECIFICATIONS (Special variations are available to the O.E.M. on special order on the models listed below)						
Replace xx in Catalog Number with value of Potentiometer in Ohms. (i.e. 09ASXP-5K)						
AGENCY APPROVALS	EN 60529 Degree of Protection	CATALOG NUMBER	DESCRIPTION	CORDSET		
c 91 0s	IP20	09ASXP-xx	Momentary	Supplied with a 6 ft. 18/4 cordset without plug. Wired three leads to potentiometer and green lead to ground.		
c 91 2 us	IP20	09ARXU-xx	Maintained			
c 91 1° us	IP20	09ASAC-xx	Momentary	Supplied with 6 ft. 18/6 cordset without plug, with auxiliary switch set to operate at the beginning of treadle stroke and wired N.O. Three leads to potentiometer and green lead to ground.		
c 91 0 us	IP20	09ARAC-xx	Maintained			
c 91 0s	IP20	0HASAC-xx	Momentary			
c '91 0'us	IP20	0HASAA-1K	Momentary	Supplied with 25' 18/6 cordset with 14 pin plug compatible with Hobart® & Miller®		
c 91 0 us	IP20	OHASAA-5KW	Momentary	Supplied with 25' 18/6 cordset with 14 pin plug compatible with Hobart® & Miller® (NOTE: Waterproof Potentiometer)		
c 711 'us	IP20	0HASAB-10K	Momentary	Supplied with 25' 18/6 cordset with 6 pin plug compatible with Lincoln®		
c '91 1 us	IP20	0HASAD-10K	Momentary	Supplied with 30' 18/6 cordset with 14 pin plug compatible with ESAB®		



Order Online www.linemaster.com 29 Plaine Hill Road POB 238 Woodstock, CT 06281-0238 USA Call: (860) 974-1000 Fax: (860) 974-0691 Fax Toll Free (US Only): (800) 974-3668

23557_Chase.indd 80 9/24/12 12:50 PM