

LINEMASTER Switch Corporation

America's Foot Switch Leader



CLIPPER FOOTSWITCH



Clipper Footswitch

Environmental Ratings:

EN 60529 Degree of Protection IP20

Key Benefits

The rugged, long life Clipper foot switch models have proved themselves in the field over many years of usage. All maintained models offer "Push On-Push Off" action that insures long trouble-free performance. The wide treadle models offer a large seven inch target for the operator's foot. Cast iron housing. Nonskid base pad. Complete with adjustable strain relief connector. Black finish.

Size: 4-1/2" x 3-1/2" x 1-1/2"

Weight: 2-1/4 lbs.

The CLIPPER TWIN consists of two SPDT or two DPDT foot switches mounted on a heavy steel base plate with nonskid pad. Divider bar between pedals helps prevent accidental operation of both pedals at one time. A tube between the two foot switches conceals all internal wiring between them. A conduit opening with strain relief connector is provided in the right foot switch.

Size:8-3/8" x 4-1/2" x 1-1/2"

Weight: 5 lbs.

Model 638-S features a cast aluminum housing painted Alert Orange with a splash resistant interior switch.



Clipper Wide Treadle Footswitch

Accessory

VINYL BOOT



SPECIFICATIONS

(Special variations are available to the O.E.M. on special order on the models listed below)



	CATALOG NUMBER					
	REGULAR TREADLE	WIDE TREADLE	DESCRIPTION	CIRCUIT	FORM	ELECTRICAL RATINGS
⊕@ (€	632-S	642-S	Momentary	SPDT	С	20 A 125-250 VAC 1 H.P. 125-250 VAC
₩.@	632-SC3*		Momentary	SPST Wired N. O.	A	15 A 125 VAC 3/4 H.P. 125 VAC
	632-SC36***		Momentary	SPDT wired N. O.	A	10 A 1/2 HP 125-250 VAC
	632-DC3A*		Maintained	SPDT wired N. O.	A	15 A 3/4 HP 125 VAC
¢Wus(€	633-S	643-S	Momentary	SPDT DB±	Z	20 A 125-250 VAC 3/4 H.P. 125 VAC 1 H.P. 250 VAC
c 91 2 us (€	635-S	645-S	Momentary	DPDT	С	15 A 125 VAC 10 A 250 VAC 1/2 H.P. 125-250 VAC
c ¶ us ⊂€	636-S	646-S	Two Stage Momentary	Each Stage SPDT	С	15 A 125 VAC 10 A 250 VAC 1/2 H.P. 125-250 VAC
(€ (€	632-DA	642-DA	Maintained	SPDT	С	20 A 125 VAC 10 A 250 VAC 1.5 H.P. 125-240 VAC
c 91 2 us	634-DA		Maintained	DPDT	С	10 A 125-250 VAC 1/8 H.P. 125 VAC 1/4 H.P. 250 VAC
⊕@	TWIN 632-S		Momentary	Each Side SPDT	С	20 A 125-250 VAC 1 H.P. 125-250 VAC
CE	TWIN 635-S		Momentary	Each Side DPDT	С	15 A 125 VAC 10 A 250 VAC 1/2 H.P. 125-250 VAC
c SU us CE			Momentary	SPDT	С	10 A 125-250 VAC 1/2 H.P. 125-250 VAC
c@Lus(€	638-SC38** (IP21)		Momentary	SPST Wired N. O.	A	10 A 125-250 VAC 1/2 H.P. 125-250 VAC

Model 638-S features a cast aluminum housing painted Alert Orange with a splash resistant interior switch.

^{*}Supplied with 8 ft. 14/3 cord and 3 prong series plug with green lead grounded.

^{**}Supplied with 8 ft. 16/3 cord, wired N.O. with green lead grounded.

^{***}Supplied with 6 ft. 18/3 cordset without plug with green lead grounded.

[±]DB Double Break models must be wired to equal voltage sources and the same polarity. The loads should be on the same sides of the line. BOLD COPY INDICATES STOCK ITEM

Clipper Wide Treadle Model

NOTE: ALL DIMENSIONS ARE FOR REFERENCE ONLY.



