



Products

Products

- [Product Type Search](#)
- [Parameter Search](#)
- [Threat Search](#)
- [Check Distributor Inventory](#)
- [Competitor Part Number](#)
- [Obsolete Parts](#)
- [Order Samples](#)
- [Product News](#)
- [New Products and Promotions](#)

Part: 111506

Series: 111 SERIES - PC BOARD MOUNT FUSE CLIP FOR 2AG OR 5X20MM DIAMETER FUSES

Technology:: Fuse Holders, Blocks and Clips - Electronic and Automotive Types



PARAMETERS

Key

PACKAGE TYPE	PKG TYPE	Fuse Clip
MOUNT METHOD	MOUNT	PC Mount
BODY STYLE FOR INTERNATIONAL SHOCK-SAFE FUSEHOLDERS	BODY	
COLOR OF DEVICE	COLOR	
FOR USE WITH THIS UL CLASS OR FUSE TYPE	FUSE TYPE	5x20mm
FOR USE WITH THIS UL CLASS OR FUSE TYPE	FUSE TYPE	
FUSE MOUNTING METHOD	FUSEMOUNTING	Axial and Radial Leaded Fuses
INDICATING	INDICATING	N
MAXIMUM CURRENT RATING	MAX (A)	5.0000
AC VOLTAGE RATING	MAX VAC (V)	125
MAX DC VOLTAGE	MAX VDC (V)	125
MOUNTING TYPE	MOUNTING	Panel Mount
	SPECIAL1	Conductive Silicone Gasket
	SPECIAL2	
TERMINAL STYLE FOR INTERNATIONAL SHOCK-SAFE FUSEHOLDERS	TERMINAL	Solder Q.C. Terminal
FOR USE WITH UL CLASS _____ FUSES	UL CLASS	Supplementary Protection



CHECK DISTRIBUTOR STOCK [\[CHECK\]](#)

REQUEST A SAMPLE [\[ADD TO CART\]](#)

Series Datasheets



111 Series Data Sheet

111.pdf (239 K)

Last Updated: May 16, 2005