

LINEMASTER Switch Corporation

America's Foot Switch Leader



CLIPPER FOOTSWITCH



Clipper Footswitch

Environmental Ratings:

EN 60529 Degree of Protection IP20

Key Benefits

The rugged, long life Clipper foot switch models have proved themselves in the field over many years of usage. All maintained models offer "Push On-Push Off" action that insures long trouble-free performance. The wide treadle models offer a large seven inch target for the operator's foot. Cast iron housing. Nonskid base pad. Complete with adjustable strain relief connector. Black finish.

Size: 4-1/2" x 3-1/2" x 1-1/2"

Weight: 2-1/4 lbs.

The CLIPPER TWIN consists of two SPDT or two DPDT foot switches mounted on a heavy steel base plate with nonskid pad. Divider bar between pedals helps prevent accidental operation of both pedals at one time. A tube between the two foot switches conceals all internal wiring between them. A conduit opening with strain relief connector is provided in the right foot switch.

Size:8-3/8" x 4-1/2" x 1-1/2"

Weight: 5 lbs.

Model 638-S features a cast aluminum housing painted Alert Orange with a splash resistant interior switch.



Clipper Wide Treadle Footswitch

Accessory

VINYL BOOT



SPECIFICATIONS

(Special variations are available to the O.E.M. on special order on the models listed below)

A WARNING

	CATALO	NUMBER				
	REGULAR TREADLE	WIDE TREADLE	DESCRIPTION	CIRCUIT	FORM	ELECTRICAL RATINGS
⊕@ (€	632-S	642-S	Momentary	SPDT	C	20 A 125-250 VAC 1 H.P. 125-250 VAC
₩.	632-SC3*		Momentary	SPST Wired N. O.	A	15 A 125 VAC 3/4 H.P. 125 VAC
	632-SC36***		Momentary	SPDT wired N. O.	A	10 A 1/2 HP 125-250 VAC
	632-DC3A*		Maintained	SPDT wired N. O.	A	15 A 3/4 HP 125 VAC
¢(U)us(€	633-S	643-S	Momentary	SPDT DB±	Z	20 A 125-250 VAC 3/4 H.P. 125 VAC 1 H.P. 250 VAC
c RI us CE	635-S	645-S	Momentary	DPDT	С	15 A 125 VAC 10 A 250 VAC 1/2 H.P. 125-250 VAC
c RI us (E	636-S	646-S	Two Stage Momentary	Each Stage SPDT	С	15 A 125 VAC 10 A 250 VAC 1/2 H.P. 125-250 VAC
(€ (€	632-DA	642-DA	Maintained	SPDT	С	20 A 125 VAC 10 A 250 VAC 1.5 H.P. 125-240 VAC
c 91 2 us	634-DA		Maintained	DPDT	С	10 A 125-250 VAC 1/8 H.P. 125 VAC 1/4 H.P. 250 VAC
(€	TWIN 632-S		Momentary	Each Side SPDT	С	20 A 125-250 VAC 1 H.P. 125-250 VAC
c ¶ Lus C €	TWIN 635-S		Momentary	Each Side DPDT	С	15 A 125 VAC 10 A 250 VAC 1/2 H.P. 125-250 VAC
c 91 2°us ⊂€	638-S		Momentary	SPDT	С	10 A 125-250 VAC 1/2 H.P. 125-250 VAC
c(U)us(€	638-SC38** (IP21)		Momentary	SPST Wired N. O.	A	10 A 125-250 VAC 1/2 H.P. 125-250 VAC

Model 638-S features a cast aluminum housing painted Alert Orange with a splash resistant interior switch.

^{*}Supplied with 8 ft. 14/3 cord and 3 prong series plug with green lead grounded.

^{**}Supplied with 8 ft. 16/3 cord, wired N.O. with green lead grounded.


^{***}Supplied with 6 ft. 18/3 cordset without plug with green lead grounded.

 $[\]pm DB$ Double Break models must be wired to equal voltage sources and the same polarity. The loads should be on the same sides of the line. BOLD COPY INDICATES STOCK ITEM

Clipper Twin with Divider Model

NOTE: ALL DIMENSIONS ARE FOR REFERENCE ONLY.







EN 60529 Degree of Protection IP20 (IP68 Upon Request)

Splash Resistant • Corrosion Resistant (Available) MEDIUM DUTY GENERAL PURPOSE DESIGN

Materials of Construction:

- Constructed of Cast Iron for long life
- Non-skid base pad
- Adjustable Strain relief connector
- Durable black finish
- Model 632-DA can be used to control lighting
- Model 638-S features a cast aluminum housing painted Alert Orange with a splash resistant interior switch

Features & Benefits:


- Proven Reliability
- All maintained models offer "Push On-Push Off" action that insures long trouble-free performance
- 2 holes provided for rigid mounting to floor or equipment

Options:

- The wide treadle models offer a large seven inch target for the operator's foot (See "Clipper - Twin & Wide Treadle" on page 34 for details)
- Available protective vinyl cover that can be applied over our Clipper. This
 boot is available only in bright orange, and provides additional protection
 to the foot switch from limited amounts of liquid, dust, dirt, mud and snow
 (See "Accessories Protective Boot" on page 75 for details)
- AirVal models available (See "Clipper Pneumatic AirVal" on page 53 for details)
- Heavy gauge steel guard available (See "Accessories Guards" on page 74 & 75 for details)

Size (HxWxD):	1.50 x 3.50 x 4.50 ln.			
Weight:	2.25 lbs.			





		CT WARNING ON PAG					
SPECIFICATIONS	(Special varia	tions are available to the	e O.E.M. on special order on the m	odels listed below)			
AGENCY APPROVALS	EN 60529 Degree of Protection	CATALOG NUMBER	DESCRIPTION	CIRCUIT	FORM	ELECTRICAL RATINGS	
⊕⊕⊕ €€	IP20	632-S	Momentary	SPDT	С	20 A 125-250 VAC 1 H.P. 125-250 VAC	
(h) (f)	IP20	632-SC3 ¹	Momentary	SPST Wired N.O.	А	15 A 125 VAC ³ /4 H.P. 125 VAC	
₩@ ·(€	IP20	632-SC36 ⁴	Momentary	SPST Wired N.O.	А	10 A 125-250 VAC ¹ / ₂ H.P. 125-250 VAC	
(h) (f)	IP20	632-DC3A ¹	Maintained	SPST Wired N.O.	С	15 A 125 VAC ³ /4 H.P. 125 VAC	
⊕ (€	IP20	633-S	Momentary	SPDT DB ³	Z	20 A 125-250 VAC ³ / ₄ H.P. 125 VAC 1 H.P. 250 VAC	
c 93 0 us (€	IP20	635-S	Momentary	DPDT	С	15 A 125 VAC 10 A 250 VAC ¹ / ₂ H.P. 125-250 VAC	
c 93 2 us (€	IP20	636-S	Two Stage Momentary	Each Stage SPDT	С		
\$ \\G (IP20	632-DA	Maintained	SPDT	С	20 A 125 VAC 10 A 250 VAC 1 1/2 H.P. 120-240 VAC	
c %X us (€	IP20	634-DA	Maintained	DPDT	С	10 A 125-250 VAC ¹ / ₈ H.P. 125 VAC ¹ / ₄ H.P. 250 VAC	
c 93 2′us (€	IP20	638-S	Momentary	SPDT	С	10 A 125-250 VAC 1/2 H.P. 125-250 VAC	
⊕ (€	IP21	638-SC38 ²	Momentary	SPDT Wired N.O.	А		

¹Supplied with 8 ft. 14/3 cord and 3 prong series plug. Green lead grounded. ²Supplied with 8 ft. 16/3 cord, wired N.O. with green lead grounded. ³DB Double Break models must be wired to equal voltage sources and the same polarity. The loads should be on the same sides of the line. ⁴Supplied with 6 ft. 18/3 cord.