

Specifications:

Sound Level Category	Extra Loud
Mode of Operation	Continuous tone
Voltage Rating	6 to 16 Vdc
Frequency	2900 Hz ±500 Hz
Loudness @ 2 FT	95 to 105 dB(A) typ. (6 to 16 Vdc)
Current Draw	20 mA Max (6 to 16 Vdc)
Housing Material	Nylon 6/6 (Color: Black)
Storage Temperature	-40°C to +85°C
Operating Temperature	-30°C to +65°C
Panel Mounting	Recommended hole size is 1.25in (31.75mm). Threaded front will fit standard 30mm (1.181in) hole.
Knurled Nut	Used to attach part to panel. The max recommended torque is 10 in-lbs
Termination	5mm standard socket used with pluggable screw terminal block.
Weight (Typical)	1.05 oz (30 g)
NEMA 3R, 4X, & 12	Approved with use of ACC03.
Options	For other options contact factory

Dimensions: Inches (mm)

RoHS Compliant

