MALLORY Mallory Sonalert Products Inc.	Part #	PK-20A38PQ
Sales Outline Drawing	Revision	A

Specifications:

Oscillation Frequency (Hz) 3800 ± 500 Operating Voltage (Vdc) $3 \sim 24$ Rated Voltage (Vdc) 12

Current Consumption (mA/max) 15 at Rated Voltage Sound Pressure Level (dB/min) 95 at 30cm at Rated Voltage

Tone/Pulse Rate (Hz0 Constant Operating Temperature (°C) $-20 \sim +70$ Storage Temperature (°C) $-30 \sim +80$

Housing ABS 757 UL94HB plastic resin (Color: Black)

Lead Pins

Weight (Grams)

Condition by wave soldering (°C)

Condition by hand soldering (°C)

Tin Plated Brass 4.8 $245 \pm 5 / 3 \pm 0.5$ sec $350 \pm 20 / \text{ within 5 sec}$

Options For other options contact factory

PS: Vp-p = 1/2 duty, square wave

RoHS Compliant

Dimensions: (units: mm)

