

**Specifications:**

<b>Sound Level Category</b>	Extra Loud
<b>Mode of Operation</b>	Fast Pulse Rate (10pps)
<b>Voltage Rating</b>	6 to 16 VDC
<b>Frequency</b>	2900 Hz ±500 Hz
<b>Loudness @ 2 FT</b>	95 to 105 dB(A) typ.
<b>Current Draw</b>	40 mA Max
<b>Housing Material</b>	Nylon 6/6 (Color: Black)
<b>Storage Temperature</b>	-40°C to +85°C
<b>Operating Temperature</b>	-30°C to +65°C
<b>Panel Mounting</b>	Recommended hole size is 1.25in (31.75mm). Threaded front will fit standard 30mm (1.181in) hole.
<b>Knurled Nut</b>	Used to attach part to panel. The max recommended torque is 10 in-lbs
<b>Weight (Typical)</b>	1.5 oz (43 g)
<b>NEMA 3R, 4X, &amp; 12</b>	Approved with use of ACC03.
<b>Options</b>	For other options contact factory

**Dimensions:** Inches (mm)

**RoHS Compliant**

