



Part Number:	WI-M-18-0
Description:	18AWG Silicone Wire Specifications

5107

-
- 18AWG Silicone Wire Specifications
 - Color: Black, PANTONE # 433 C / 426 C
 - Standards: UL style 3577
 - Rating: 150 ° C / -80 ° C, 3000V, 22A
 - Conductivity: 18AWG (copper)

413/44 AWG (7/ 59 / 0.05 mm)

7 bundles / 59 strands per bundle / Φ 0.05 mm / per strand

- Insulation: Silicone Rubber

Coating thickness: 0.047 (1.19 mm)

Overall diameter: 0.140 ± 0.002 (3.56 mm \pm 0.05 mm)