

BII-00000-\* Part # color

\* 0 - Black 5 - Green 2 - Red 6 - Blue 4 - Yellow 9 - White



1 | 2 | 3 | 4 | 5 | 6 | 7 | 8 | 9 | 10 | 11 | 12 | 13 | 14 | 15 | 16 | 17 | 18 Page 9



Shrouded Double Banana Plug-Both Ends BU-7171- B -00-0 with RG58 BU-7171- F -00-0 with RG174 BU-7171- L -00-0 with Twisted Pair Cable

- 0.75" centers.
- Shielded #22 AWG (7/30) twisted pair cable, connected to (-) side of plug.
- Nine-leaf beryllium copper nickel-plated cage spring.
- Shielded RG58C/U, MIL-C-17F 50 ohm.
- Shielded RG174/U, MIL-C-17D 50 ohm.
- Product Data Sheet & Compatibility Info.
- Send us your questions about this product

Stackable Double Banana Plug-Both Ends BU-7070- B -00-\* with RG58 BU-7070- F -00-\* with RG174

- Nine-leaf beryllium copper, nickel-plated spring.
- Stacks in multiples.
- Shielded RG58C/U, MIL-C-17F 50 ohm coaxial cable.
- Shielded RG174/U, MIL-C-17D 50 ohm coaxial cable.
- **Product Data Sheet**
- Send us your questions about this product





## BU-8080-E-00-\* 0.025" (0.6mm) Square Pin Receptacle/Both Ends

- Ideal patch cord for PC Boards.
- Pin Receptacle: with 0.025" (0.6 mm) copper-nickel-tin alloy725 with gold contact plating.
- ABS housing.
- #22 AWG (19/34) tinned copper with 105°PVC insulation.
- Product Data Sheet
- Send us your questions about this product

## BU-0070-F-00-\* Stackable Double Banana Plug to RG174

- Nine-leaf beryllium copper, nickel-plated springs.
- Multiple stacking.
- Coaxial Cable: shielded RG174/U, MIL-C-17-D 50 ohm.
- Product Data Sheet
- Send us your questions about this product



Enlarge

## Contents | Next Home | Insulated BNCs | Clips & Insulators | Insulated Test Accessories Accessories & Probes | Kits | Cross Reference

 $\ \odot$  1999-2000 Mueller Electric Company. All rights reserved. Problems with the site should be reported to the <u>webmaster</u>.