



BU-00000- *
Part # color | * 0 - Black 5 - Green
2 - Red 6 - Blue
4 - Yellow 9 - White

TEST LEADS

[1](#) | [2](#) | [3](#) | [4](#) | [5](#) | [6](#) | [7](#) | [8](#) | [9](#) | [10](#) | [11](#) | [12](#) | [13](#) | [14](#) | [15](#) | [16](#) | [17](#) | [18](#) Page 7

BU-3156-C-00-0

Insulated Mini-Alligator Clips To Insulated BNC

- Nickel-plated steel; PVC insulator (No. 31); jaw opening 3/16" (5mm).
- Red (+) clips have 2" (51 mm) lead wires.
- Black (-) clips have 7" (178 mm) lead wires.
- Molded "Y" block prevents separation and corrosion.
- BNC Male Connector gold-plated center, silver-plated body.
- Shielded RG58C/U, MIL-C-17F.
- #20 AWG wire (41/36) tinned copper with 105°C PVC insulation.
- [Product Data Sheet](#)
- [Send us your questions about this product](#)



BU-3131-A-00-*

Insulated "Mini-Alligator" Clip-Both Ends

- Nickel-plated steel; jaw opens to 3/16" (4.7 mm).
- PVC clip insulator (No. 31).
- #20 AWG (41/36) tinned copper hook-up wire; with 105°C PVC insulation.
- [Product Data Sheet](#)
- [Send us your questions about this product](#)



[Enlarge](#)

BU-3180-E-00-*

Insulated "Mini-Alligator" Clip To 0.025" (0.6mm) Square Pin Receptacle

- Nickel-plated steel with PVC insulator (No. 31); jaw opens to 3/16" (4.7 mm).
- Pin Receptacle is copper-nickel-tin alloy 725.
- ABS housed, 0.000030" (0.00076 mm) gold-plated conductor.
- Hook-up Wire: #22 AWG (19/34) tinned copper with 105°C PVC insulation.
- [Product Data Sheet](#)
- [Send us your questions about this product](#)



BU-4444-A-00-*

Stackable 0.080" (2.0 mm) Pin Plug—Both Ends

- Pin tip is 0.080" (2.0 mm) dia.; 0.500" (12.7mm) long.
- Tip jack accepts 0.080" (2.0 mm) dia. pin jack contact.
- Nickel-plated beryllium copper spring.
- ABS housing.
- Hook-up Wire: #20 AWG (41/36) tinned copper with 105°C PVC insulation.
- [Product Data Sheet](#)
- [Send us your questions about this product](#)



[Enlarge](#)

[Contents](#)|[Next](#)

[Home](#)|[Insulated BNCs](#)|[Clips & Insulators](#)|[Insulated Test Accessories](#)
[Accessories & Probes](#)|[Kits](#)|[Cross Reference](#)

©1999-2000 Mueller Electric Company. All rights reserved.
Problems with the site should be reported to the [webmaster](#).