

Shrouded Banana Plug to Safety Test Prod BU-4061-M-39-* (Silicone) BU-4061-N-39-* (PVC - 1000V, 20 Amp)

- IEC 1010 coompliant
- Nine-leaf cage spring 4 mm shrouded plug
- Stainless steel tip with 8-32 thread
- Molded housing
- Product Data Sheet
- Send us your questions about this product

Shrouded Right Angle Banana Plug to Safety Test Prod BU-4062-M-39-* (Silicone) BU-4062-N-39-* (PVC - 1000V, 20 Amp)

- IEC 1010 coompliant
- Nine-leaf cage spring 4 mm shrouded plug
- Stainless steel tip with 8-32 thread
- Molded housing
- Product Data Sheet
- Send us your questions about this product





Shrouded Banana Plugs, Both Ends BU-6161-M-39-* (Silicone) BU-6161-N-39-* (PVC - 1000V, 20 Amp)

- IEC 1010 coompliant
- Nine-leaf beryllium, nickel-plated springs
- Insulated 4mm plugs; exclusive free rotation
- provides constant positive contact with minimun resistance
- Molded housing
- Product Data Sheet
- Send us your questions about this product

Shrouded Banana Plugs, Both Ends BU-6162-M-39-* (Silicone) BU-6162-N-39-* (PVC - 1000V, 20 Amp)

- IEC 1010 coompliant
- Nine-leaf beryllium, nickel-plated springs
- Straight, right angle 4mm plugs; exclusive free rotation
- provides constant positive contact with minimun resistance
- Molded housing
- Product Data Sheet
- Send us your questions about this product

