



Soldering Tips - 3/16" Pace Compatible

33 Series

Plato is one of the largest manufacturers of soldering tips in the world, producing tips to fit all of the most popular soldering stations. The long life and fast heat recovery of Plato soldering tips increases user effectiveness and decreases production times. All Plato soldering tips manufactured since January 2004 are tinned with Lead-Free solder.

Long Life: Using a high quality Plato soldering tip increases soldering speed and decreases the total cost of manufacture. Higher temperatures and high tin content solders, common in lead-free soldering processes, place additional strain on soldering iron tips. The long life of a Plato soldering iron tip reduces tip changes, decreasing the total number of tips used and decreasing production time.

Rapid Heat Recovery: Plato soldering tips are constructed from highly conductive premium grade copper to transmit heat to the work more quickly than other brands of soldering tips. This quick heat recovery enables more joints to be soldered per minute, thus reducing manufacturing time and costs.



3/16" tips for Pace PS-90, PS-80, SP2A and IR70

Plato is one of the largest manufacturers of soldering tips in the world, producing tips to fit all of the most popular soldering stations. The long life and fast heat recovery of Plato soldering tips increases user effectiveness and decreases production times.

- Fast heat recovering increases soldering speed
- Longer tip reduces manufacturing costs
- Fewer tip change overs



Product Packaging

33-6055
Screwdriver
1.5mm
10 units/case



33-8142
Conical
0.8mm
10 units/case



33-6058
Screwdriver
3.2mm
10 units/case



33-8141
Point
0.4mm
10 units/case



33-1658
Screwdriver
4.8mm
10 units/case



33-1144
Screwdriver
0.8mm
10 units/case



33-6057
Screwdriver
2.4mm
10 units/case



33-1146
Angled SMD
1.2mm
10 units/case



Techspray
P.O. Box 949, Amarillo, TX 79105
800-858-4043 • www.techspray.com



33-8143
Angled SMD
 0.5mm
 10 units/case



SMP-2004
Knife
 6.3mm
 10 units/case



33-5894
Bevel
 3.2mm
 10 units/case



33-6056
Screwdriver
 1.5mm
 10 units/case



33-5895
SMD flow tip
 3.4mm
 10 units/case



33-1147
Screwdriver
 1.5mm
 10 units/case



33-3981
Point, micro
 0.4mm
 10 units/case




33-3982
Angled SMD, micro
 0.4mm
 10 units/case



33-7107
Bevel
 3.2mm
 10 units/case



33-7103
Screwdriver
 1.6mm
 10 units/case





Technical Information

Environmental Policy

Techspray is committed to developing products to ensure a safer and cleaner environment. We will continue to meet and sustain the regulations of all federal, state and local government agencies.

Resources

Techspray products are supported by a global sales, technical and customer services resources.

For additional technical information on this product or other Techspray products in the United States, call the technical sales department at 800-858-4043, email tsales@techspray.com or visit our web site at: www.techspray.com.

North America

Techspray
P.O. Box 949
Amarillo, TX 79105
800-858-4043
Email: tsales@techspray.com

Europe

ITW Contamination Control
Saffierlaan 5
2132 VZ Hoofddorp
The Netherlands
+31 88 1307 400
Email: info@itw-cc.com

Countries Outside US

Call to locate a distributor in your country.

Important Notice to Purchaser/User: The information in this publication is based on tests that we believe are reliable. The results may vary due to differences in tests type and conditions. We recommend that each user evaluate the product to determine its suitability for the intended application. Conditions of use are outside our control and vary widely. Techspray's only obligation and your only solution is replacement of product that is shown to be defective when you receive it. In no case will Techspray be liable for any special, incidental, or consequential damages based on breach of warranty, negligence or any other theory.

© 2014 Techspray, A Division of ITW