

**Olympic Wire and Cable**

7 Madison Road • Fairfield, NJ 07004


973.227.7996 800.526.2269 • Fax: 973.227.1606

email: sales@olympicwire.com

---

**Olympic P/N 314, MIL-W-16878/4, TYPE E, NEMA HP3 Wire**

---



**MIL-W-16878/4, TYPE E, NEMA HP3 Wire**

Single conductor stranded silver plated Copper extruded PTFE insulation.

**Characteristics:**


Temperature rating — 65°C to +200°C.

Voltage rating 600 Volts. Resistant to acids, alkalis, oil, flame, moisture, solvents, and fungus.

UL Rated - 105°C

---

**SPECIFICATIONS**

Conductor Size	12 AWG
Stranding	19/25 Silver Plated Copper
Insulation	PTFE
Nom. Wall Thickness	0.012 in
Nom. O.D.	0.113 in
Military Spec.	MIL-W-16878/4
Military Rating	600 V, -70°C to 200°C
Color Code	Hook Up Wire Color Code Chart
RoHS Compliant	 RoHS Compliant