

Olympic Wire and Cable

7 Madison Road • Fairfield, NJ 07004

973.227.7996 800.526.2269 • Fax: 973.227.1606

email: sales@olympicwire.com

Olympic P/N 2405, SOOW Control Cable



SOOW Control Cable

Multiconductors

Stranded bare Copper conductors, separator, color coded EPDM insulation, conductors twisted with fillers as needed, separator, black oil-resistant CPE jacket, UV resistant

Applications:

For use in all types of remote control and signal circuits where a flexible, oil-resistant cable is required

Temperature Ratings:-40°C +90°C

SPECIFICATIONS

Conductor Size	18 AWG
Stranding	16/30 Bare Copper
No. of Conductors	5
Insulation	EPDM
Nom. Insulation Thickness	0.030 in
Jacket	CPE, Black
Jacket Thickness	0.080 in
Nom. O.D.	0.465 in
Color Code	Black Green Orange Red White
Voltage	600 V
Operating Temperature	-40 to 90 °C
Weight per 1000 ft	119 lb

RoHS Compliant



RoHS Compliant