

Olympic Wire and Cable

7 Madison Road • Fairfield, NJ 07004

973.227.7996 800.526.2269 • Fax: 973.227.1606

email: sales@olympicwire.com

Olympic P/N 1112, Duplex Thermocouple Grade Cable




Duplex Thermocouple Grade Cable

Solid or stranded alloy wire matched and calibrated to standard limits of error per ASA C96.1

Applications:

For primary thermocouple fabrication and interconnection of thermocouples to temperature recording apparatus

SPECIFICATIONS

Grade Designation	K
Conductor Size	20 AWG
Stranding	ONE
Insulation	Glass Braid
Jacket	Glass Braid, Brown / Yellow
Nom. O.D.	0.064 x 0.109 in
Operating Temperature	482 °C
Positive Wires	Chromel - Yellow
Negative Wires	Alumel - Red
RoHS Compliant	 RoHS Compliant