

Olympic Wire and Cable

7 Madison Road Fairfield, NJ 07004

973.227.7996 800.526.2269 Fax: 973.227.1606

email: sales@olympicwire.com

Olympic P/N 6357E, TPE Jacket Coiled Cords, SVEO, SJEOW, SEOW



TPE Jacket Coiled Cords, SVEO, SJEOW, SEOW

Retracted Lengths 1, 2 & 4 Feet - Extended Lengths 5, 10 & 20 Feet

Long-lasting service is assured with this quality multiconductor power cord. Each conductor is stranded copper, with TPE insulation, and a rugged weather and oil resistant TPE jacket overall.


Application:

Used on electric tools, portable drills, soldering irons, electrical appliances, household appliances, etc., to eliminate loose hanging wires and to prevent wires from tangling and twisting.

· [SPECIFICATIONS](#) · [COMPETITOR CROSS REFERENCE PART NUMBERS](#)

SPECIFICATIONS

Conductor Size	16 AWG
Stranding	65/34, Bare Copper
No. of Conductors	3
Insulation	TPE
Jacket	TPE, Black
Cable O.D.	1 13/16 in
Coil O.D.	0.470 in
UL Style	SEOW
Color Code	Black, White, Green
Voltage	600 V
Operating Temperature	-20 to +90 °C
Cord Length	4 ft
AMP Rating	10
Tangent Leads ¹	6 in

RoHS Compliant	 RoHS Compliant
----------------	---

1 12 inch retracted lengths have 12 inch tangent leads. 24 inch, 36 inch, and 48 inch retracted lengths have 6 inch tangent leads.

COMPETITOR CROSS REFERENCE PART NUMBERS

Alpha P/N	670/4
-----------	-------