

Olympic Wire and Cable

7 Madison Road • Fairfield, NJ 07004

973.227.7996 800.526.2269 • Fax: 973.227.1606

email: sales@olympicwire.com

Olympic P/N 2025, Audio and Control, Unshielded, Multiconductor Cable**Audio and Control, Unshielded, Multiconductor Cable**

UV RESISTANT
CE MARKED

SPECIFICATIONS

No. of Conductors	25
Conductor Size	22 AWG
Stranding	7/30, Tinned Copper
Insulation	PVC
Nom. Wall Thickness	0.010 in
Jacket	PVC, Chrome, Sunlight Resistant
Nom. Jacket Thickness	0.032 in
Nom. O.D.	0.364 in
UL Style	2464, CM
UL Flame Test	VW-1
CSA Type	C (UL) AWM I/II A/B
CSA Flame Test	FT-4
European Conformity	CE
Color Code	Color Code Chart 8
Voltage	300 V
Operating Temperature	-20 to 105 °C

RoHS Compliant



RoHS Compliant