

Olympic Wire and Cable

7 Madison Road • Fairfield, NJ 07004


973.227.7996 800.526.2269 • Fax: 973.227.1606

email: sales@olympicwire.com

Olympic P/N 2315, CE COMPLIANT, Audio and Control, Unshielded, Multiconductor Cable



SPECIFICATIONS

No. of Conductors	15
Conductor Size	16 AWG
Stranding	19/29, Tinned Copper
Insulation	PVC
Nom. Wall Thickness	0.030 in
Jacket	PVC, Chrome
Nom. Jacket Thickness	0.060 in
Nom. O.D.	0.694 in
UL Style	2501
UL Flame Test	VW-1
CSA Type	cRU AWM I/II A/B
Color Code	Color Code Chart 2
Voltage	600 V
Operating Temperature	-20 to 80 °C
RoHS Compliant	 RoHS Compliant