

## Olympic Wire and Cable

7 Madison Road • Fairfield, NJ 07004

973.227.7996 800.526.2269 • Fax: 973.227.1606

email: sales@olympicwire.com

## Olympic P/N 2884, Sound/Broadcast Audio, Foil Shielded Cable



### Sound/Broadcast Audio, Foil Shielded Cable

Tinned Copper, Polyethylene insulated, Conductors twisted, Aluminum Mylar shield, 20 AWG stranded tinned Copper drain wire, Chrome PVC jacket.

#### Temperature Rating

-20°C to 60°C

## SPECIFICATIONS

Conductor Size	20 AWG
Stranding	7/28, Tinned Copper
No. of Conductors	3
Insulation	Polyethylene
Nom. Insulation Thickness	0.016 in
Shielding	Aluminum mylar with stranded TC drain wire
Jacket	PVC, Chrome, Sunlight Resistant
Nom. Jacket Thickness	0.028 in
Nom. O.D.	0.208 in
UL Style	2093, CM
UL Flame Test	VW-1
Color Code	Black Clear Red
Working Voltage	350 V
UL Voltage	300 V
Operating Temperature	-20 to 60 °C

RoHS Compliant



RoHS Compliant