

Olympic Wire and Cable

7 Madison Road • Fairfield, NJ 07004

973.227.7996 800.526.2269 • Fax: 973.227.1606


email: sales@olympicwire.com

Olympic P/N 2005SHD, Foil Shielded, PVC Jacketed, Control Cable**Foil Shielded, PVC Jacketed, Control Cable**

UV RESISTANT
CE MARKED

SPECIFICATIONS

Conductor Size	22 AWG
Stranding	7/30 Tinned Copper
No. of Conductors	5
Insulation	PVC
Nom. Wall Thickness	0.010 in
Shielding	Aluminum mylar with stranded TC drain wire
Jacket	PVC, Chrome
Nom. Jacket Thickness	0.035 in
Nom. O.D.	0.212 in
UL Style	2464 CM
UL Flame Test	VW-1
CSA Type	AWM I/II A/B
CSA Flame Test	FT-4
Color Code	Black Green Orange Red White
Voltage	300 V
Operating Temperature	-20 to 105 °C

Nominal Capacitance ¹	35 pF/ft
RoHS Compliant	 RoHS Compliant

¹ Capacitance between conductors