



FIRE ALARM ECONOMY GRADE

**POWER LIMITED
60°C-300 VOLTS
FIRE-PROTECTIVE
SIGNALING CABLE**

RISER RATED

**UL CLASSIFIED FPLR,
NEC 760**

UNSHIELDED

DESCRIPTION:
Solid bare copper,
vinyl insulated,
conductors cabled,
red vinyl jacket

OLYMPIC NO.	NO. OF COND.	AWG SIZE	CAPACIT. COND. TO COND.	JACKET THICKNESS	NOM. O.D.
3106L	2	18	20.0 pF/ft.	.014"	.145"
3109L	4	18	20.0 pF/ft.	.014"	.170"
3109/6	6	18	20.0 pF/ft.	.014"	.200"
3109/8	8	18	20.0 pF/ft.	.014"	.220"
3112L	2	16	20.0 pF/ft.	.014"	.170"
3115L	4	16	20.0 pF/ft.	.014"	.195"
3118L	2	14	21.0 pF/ft.	.014"	.210"
3119L	4	14	20.0 pF/ft.	.014"	.250"
3122L	2	12	22.0 pF/ft.	.014"	.245"

SHIELDED

DESCRIPTION:
Solid bare copper,
vinyl insulated,
conductors cabled,
with aluminum mylar shield and
#22-7 tinned copper drain wire*,
red vinyl jacket

*#16-7 tinned copper drain wire for cables with #14 and #12 conductors

OLYMPIC NO.	NO. OF COND.	AWG SIZE	INSUL. THICKNESS	JACKET THICKNESS	NOM. O.D.
3108L	2	18	.009"	.014"	.150"
3110L	4	18	.009"	.014"	.175"
3110/6	6	18	.009"	.014"	.205"
3110/8	8	18	.009"	.014"	.235"
3114L	2	16	.009"	.014"	.170"
3116L	4	16	.009"	.014"	.200"
3120L	2	14	.013"	.014"	.215"
3124L	2	12	.013"	.014"	.245"

COLOR CODE: Black, Red, Yellow, Blue, Brown, Orange, Green, White