

Olympic Wire and Cable

7 Madison Road • Fairfield, NJ
07004 973.227.7996
800.526.2269 • Fax:
973.227.1606
email: sales@olympicwire.com

Olympic P/N 2826 : Overall Foil Shielded, PVC Jacketed, Sunlight Resistant, Control Cable



Overall Foil Shielded, PVC Jacketed, Sunlight Resistant, Control Cable

UL 2464

DESCRIPTION

Tinned copper, PVC insulated, conductors twisted, aluminum mylar shield with 24AWG stranded tinned copper drain wire, chrome PVC jacket.

Temperature Rating

-20 to 105 °C

SPECIFICATIONS

No of Conductors	6
Conductor Size	24 AWG
Stranding	7/32 Tinned Copper
Insulation	SR, PVC
Nom Wall Thickness	0.010 in
Shielding	Aluminum Mylar with stranded TC drain wire
Jacket	PVC, Chrome
Nom Jacket Thickness	0.035 in
Nom OD	0.215 in
UL Style	2464, CM, CMG
UL Flame Test	VW-1
CSA Type	C (UL)
CSA Flame Test	FT-4

Voltage	300 V
Operating Temperature	-20 to 105 °C
Nominal Capacitance (Capacitance between conductors)	30 pF/ft
Color Code	Color Code Chart 1
Compliance	CE
RoHS Compliant	