



FEATURES:

- Banana plugs are internally shorted with #18 AWG wire.
- Banana plugs can be vertically and horizontally stacked for test versatility.
- Banana plug springs are Nickel Plated, Beryllium Copper for long insertion cycle life.

MATERIALS:

Banana Jacks: Brass, Nickel Plated

Banana Plug: Body - Brass, Nickel Plated

Spring: Beryllium Copper, Nickel Plated

Insulation: ABS, Color: Per Part Number

Marking: "MDP-S, POMONA ELECTRONICS CO, INC. POMONA, CALIFORNIA",
"SHORTING BAR"

RATINGS:

Operating Voltage: 5000 VDC Max.

Operating Temperature: +50°C (+122°F) Max.

Current: 15 Amperes

ORDERING INFORMATION: Model MDP-S-*

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ±.005" (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies.

Made in USA