



MATERIALS:

- Body and Fittings - Brass
- Center Contact (Male) – Gold Plated Brass
- Center Contact (Female) – Gold Plated Beryllium Copper
- Outer Contact (Male) – Gold Plated Brass
- Gasket/Seal – Silicone Rubber

Finish:

- Body and Fittings – White Bronze Plating
- Center Contact (M) – Gold Plated Brass
- Center Contact (F) – Gold Plated Beryllium copper
- Outer Contact (M) – Tarnish Resistant

RATINGS:

- Operating Voltage: 1000 VRMS
- Nominal Impedance: 50 Ohms
- Dielectric – PTFE

ORDERING INFORMATION: Model 3843

All dimensions are in inches. Tolerances (except noted): .xx = ± 0.02 " (.51 mm), .xxx = ± 0.005 " (.127 mm).
All specifications are to the latest revisions. Specifications are subject to change without notice.
Registered trademarks are the property of their respective companies.

Made in USA