



FEATURES:

• Bantam plugs are molded directly to the cable for optimum durability

MATERIALS:

Bantam Plug: Body – Brass, Insulation – PVC, Color: Black Audio Cable: Two Conductor Twisted Pair With Spiral Shield, Color: Gray Capacitance: 40 pF/Ft. Conductors: 22 AWG, Stranding: 7 x 30 Jacket: PVC, O.D. .180" (4,6mm) Nom., Marking: "POMONA 4279-XX" Finish: 4279N Brass nickel plated

RATINGS:

Operating Temperature: +50°C (+122°F) Operating Voltage: 300 VRMS

ORDERING INFORMATION: XX = Cable Length, Standard Lengths:

Model 4279-XX :12" (30,5 cm), 24" (61 cm), 36" (91,44cm), 48" (121,92cm), 60" (152,4cm) 4279N-XX: 24" (61 cm), 36" (91,44cm), 60" (152,4cm) Additional lengths can be quoted upon requested. Ordering Example: 4279-12, Cable length is 12" with non-plated Bantam connector 4279N-24, Cable length is 24 with brass nickel plated Bantam connector

All dimensions are in inches. Tolerances (except noted): $.xx = \pm .02$ " (,51 mm), $.xxx = \pm .005$ " (,127 mm). All specifications are to the latest revisions. Specifications are subject to change without notice. Registered trademarks are the property of their respective companies. Made in USA