



### FEATURES:

- Permits a standard 2 conductor 6.4 (.250) dia. phone plug to be used with equipment having Banana Jacks or Binding Posts.
- Cross holes 4.2 (.166) in body provide side stackup connections.

### MATERIALS:

Upper Conn: Phone Jack – 2 Conductor

Material: Brass.

Finish: Nickel plated.

Insulation: ABS molded to Phone Jack and Banana Plug bodies.

Color: Black

Marking: “4044 POMONA ELECTRONICS.”

Lower Conn: Double Banana Plug

Material: Spring – Beryllium Copper, Berylco 25 per QQ-C-533.

Body – Brass per QQ-B-626, Alloy 360, ½ Hard.

Finish: Nickel plated per QQ-N-290, Class 2, 200/300 microinches.

### RATINGS:

Operating Temperature: +50° C. (+122° F.) Max.

Operating Voltage: 500 VRMS.

### ORDERING INFORMATION: Model 4044

All dimensions are in inches. Tolerances (except noted): .xx = ±.02” (.51 mm), .xxx = ±.005” (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA