

**Models 7140, 7142, 7148, 7150, 7151, 7152, 7153
Cable Mounted 1/4" Phone Plugs and Jack**



Model 7140 1/4" Phone Plug 2 Conductor (Mono)



Model 7142 1/4" Phone Plug 3 Conductor (Stereo)



Model 7148 1/4" Phone Jack-Locking (Stereo or Mono)



Model 7150 1/4" Phone Plug 2 Conductor (Mono)-Long Handle



Model 7151 1/4" Phone Plug 2 Conductor (Mono)-Right Angle



Model 7152 1/4" Phone Plug 3 Conductor (Stereo)



Model 7153 1/4" Phone Plug 2 Conductor (Mono)-Large Diameter Cable

Use for optimal audio signal transfer and secure connection.

Features

- Available in mono and stereo versions
- Two and three conductor versions
- Quick to assemble
- Rugged all metal housing

Materials

- Body for models, 7140, 7142, 7148, 7151 is diecast zinc alloy with tarnish resistant nickel-plating
- Sturdy strain relief clamp (7140, 7142, 7148): POM.
- Plugs are nickel-plated brass

Ordering Information

Model: 7140, 7142, 7148, 7150, 7151, 7152, 7153.

Specifications

MODEL	WIRE SIZE (AWG)	O.D.	POLES
7140	18 AWG / 1 mm ²	4-7 mm	2 (Mono)
7142	18 AWG / 1 mm ²	4-7 mm	3 (Stereo)
7148	18 AWG / 1 mm ²	4-7 mm	2 or 3 (Mono or Stereo)
7150	18 AWG / 1 mm ²	12 mm	2 (Mono)
7151	18 AWG / 1 mm ²	4-7 mm	2 (Mono)
7152	16 AWG / 1.5 mm ²	12 mm	3 (Stereo)
7153	16 AWG / 1.5 mm ²	17.5 mm	2 (Mono)

USA: Sales: 800-490-2361 Technical Support: 800-241-2060 Fax: 888-403-3360

Europe: 31-(0) 40 2675 150 **International:** 425-446-5500

e-mail: technicalsupport@pomonatest.com

Where to Buy: www.pomonaelectronics.com

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ±.005" (.127 mm). All specifications are to the latest revisions. Specifications are subject to change without notice. Registered trademarks are the property of their respective companies.