

Models 72906 Mini SMD Grabber Test Clips



Mini SMD Grabber Test Clips

Features

- Designed for easy attachment to SMD chips with pitches down to 0.032" (0.80 mm)
- Insulated shaft can be bent up to 36 degrees for versatile attachment in awkward locations or close proximity to other clips
- Rotating jaws increase versatility in connection and stacking.
- Thin (3mm) profile allows close placement to adjacent clips.
- Compatible with leads with Ø0.8 mm female connectors
- Order Pomona model number 72905-0 for clip lead for SMD Mini Grabber - 0.8mm female/4 mm female for easy attachment to standard test leads.

Materials


• Insulation: Polyamide

Jaws: Steel

Ordering Information

Model: 72906-Color

Available colors: Black (-0), Red (-2)



Specifications

Max Current Admissible	1A
Voltage; Max - Tension	33 V AC / 70 V DC
Temperature	-20° C + 80° C
Max Resistance	Less than 15 mΩ

Rating: hands free testing in controlled environment: 70Vrms max. For CE compliance: Not intended for handheld use at voltages above 33Vrms/70Vdc

USA: Sales: 800-490-2361 Technical Support: 800-241-

2060 Fax: 888-403-3360

Europe: 31-(0) 40 2675 150 **International**: 425-446-5500

e-mail: technicalsupport@pomonatest.com
Where to Buy: www.pomonaelectronics.com

All dimensions are in inches. Tolerances (except noted): $.xx = \pm .02$ " (,51 mm), $.xxx = \pm .005$ " (,127 mm). All specifications are to the latest revisions. Specifications are subject to change without notice. Registered trademarks are the property of their respective companies.