


# Model 73047 N Type Jack to UHF Plug Adapter





Model 73047 N Type Jack to UHF Plug Adapter

#### Features

- DC 300MHz bandwidth.
- Connectors are precision machined.

### **Materials**

Center Conductor: Phosphor Bronze, Gold Plated Connector Body: Brass, Nickel Plated Insulators: PTFE

# **Specifications**

Frequency Range:	DC – 300MHz
Contact Resistance:	
Center Conductor:	≤1.0 mΩ
Outer Conductor:	≤0.2 mΩ
Insulation Reistance:	≥ 300 MΩ
Dielectric Withstand Voltage:	750V
For CE compliance, do not hold in hand when	
voltages exceed 33 Vrms / 70 Vdc.	
Number of Insertions:	500 cycles minimum

# **Ordering Information**

Model: 73047

USA: Sales: 800-490-2361 Technical Support: technicalsupport@pomonatest.com Fax: 425-446-5844 Europe: 31-(0) 40 2675 150 International: 425-446-5500 Where to Buy: www.pomonaelectronics.com All dimensions are in inches. Tolerances (except noted):  $.xx = \pm .02$ " (,51 mm),  $.xxx = \pm .005$ " (,127 mm). All specifications are to the latest revisions. Specifications are subject to change without notice. Registered trademarks are the property of their respective companies.