
Pomona®

Model 6718 Dual Output, 75 Ohm BNC Circuit Board Mount, White Valox Case



Materials:

Case White Valox
BNC Body Nickel plated brass
Center Contact Pin Gold plated brass

Center Contact Socket Gold plated phosphor bronze
Insulator Polybutylene Terephthalate

Ratings:

Impedance: 75 Ohms
Frequency: 0 to 4 GHz
VSWR: 1.30 max

Contact Resistance: 3 Milliohms max.

Voltage * 500 V

Insulation Resistance: 5,000 Megohms min.

Insertions: 500

Temperature: -40 to +85 C

Shock 50 G

Vibration 20 G from 80 to 2000 Hz

All dimensions are in inches. Tolerances (except noted): $.xx = \pm .02$ " (,51 mm), $.xxx = \pm .005$ " (,127 mm). All specifications are to the latest revisions. Specifications are subject to change without notice. Registered trademarks are the property of their respective companies. Made in USA

Sales: 800-490-2361 Fax: 888-403-3360 Technical Assistance: 800-241-2060 For "Where to Buy" information, visit the Pomona web site at www.pomonaelectronics.com

Rev: 002 D1099687

^{*} Hands free testing in controlled voltage environment: For CE compliance: not intended for hand held use at voltages above 33 Vrms / 70 Vdc.