



FEATURES:

- High visibility bright yellow body.
- Color-coded cap for identification.
- Mates with any .080 tip DMM test probe.
- Connect to insulated wires without cutting into insulation.
- Fits wires from 0.030" diameter through 0.180" diameter insulation.
- Spring loaded slider holds wire centered for piercing needle.
- Rotating jack will not twist test lead while the needle is screwed into wire.

MATERIALS:

Body and Knob: Nylon

Tip: Stainless Steel

Spring: Steel

Jack: Brass

RATINGS:

Operating Voltage: 30VAC or 60VDC Max.

Current: 1 Amperes Max.

ORDERING INFORMATION: Model 6413 (Includes a set of one Black/Yellow and one Red/Yellow)

All dimensions are in inches. Tolerances (except noted): .xx = $\pm .02$ " (.51 mm), .xxx = $\pm .005$ " (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA